





NOTES:

1. ALL DIMENSIONS SHOWN IN TABLE ARE IN INCHES, UNLESS OTHERWISE NOTED & ARE ± 1 INCH (25MM).
2. ALL ITEMS SHOWN IN PHANTOM LINE ARE TO BE PROVIDED BY OTHERS.
3. ALL DIMENSIONS ARE SUBJECT TO CHANGE WITHOUT ANY NOTICE.
4. INSTALL UNIONS FITTINGS ON INLET & OUTLET PLUMBING CONNECTIONS.
5. PROVIDE A 2 FEET MINIMUM CLEARANCE ABOVE MINERAL TANK FOR FILLING MEDIA.
6. FOR INSTALLATIONS USING METAL PLUMBING, CONNECT A METAL BONDING STRAP TO INLET & OUTLET METAL PLUMBING TO MAINTAIN ELECTRICAL CONTINUITY.
7. PROVIDED SYSTEM SHALL NOT BE SUBJECT TO ANY VACUUM. IF RISK OF VACUUM IS PRESENT, INSTALL VACUUM RELIEF VALVE WATTS ORDERING CODE # 0556031 ON OUTLET LINE.
8. THE FULL WEIGHT OF THE PIPING AND VALVES MUST BE SUPPORTED BY PIPE HANGERS OR OTHER MEANS.
9. INLET AND OUTLET HEADERS NEED TO BE SIZED ACCORDING TO FLOW RATE REQUIREMENTS BY OTHERS.
10. LIMIT INLET PRESSURE TO NOT EXCEED MAXIMUM PUBLISHED OPERATING PRESSURE.
11. USE DIELECTRIC UNIONS ON PLUMBING CONNECTIONS WHEN DISSIMILAR METALS ARE PRESENT.

MODEL OF1260-30TM ONEFLOW ANTI-SCALE SYSTEM DIMENSIONS (INCHES) & SPECIFICATIONS													
MODEL NO.	ORDERING CODE (EDP NO.)	MINERAL TANK SIZE	INLET	OUTLET	OVERALL HEIGHT (SEE NOTE 5)	OVERALL DEPTH	OVERALL WIDTH	SYSTEM INLET/OUTLET PIPE SIZE CONN. (NPT)	PEAK SERVICE FLOW GPM	MIN/MAX OPERATING TEMP F°	MIN/MAX OPERATING PRESSURE (PSI)	ESTIMATED OPERATING WEIGHT (LBS)	ESTIMATED SHIPPING WEIGHT (LBS)
OF1260-30TM	0002207	12 X 60	62.2	62.2	63.7	12.10	12.10	2.0	30.00	40/100	15/100	394.00	72.00

		815 CHESTNUT ST NORTH ANDOVER, MA 01845		TITLE: GENERAL INSTALLATION, MODEL OF1260-30TM ONEFLOW ANTI-SCALE SYSTEMS		PART NO.: SEE TABLE	
ORDER NO.: 7/7/2021 DATE: 7/7/2021 REV: 1 OF 3		SHEET NO.: 1 OF 3 SUPERSEDES: SEE TABLE		MATERIAL: N/A		EST. WEIGHT: SEE TABLE	
FILE TYPE: CAD		D 1		REV: 1		SEE TABLE	




CLIENT PROJECT SIGN-OFF	
JOB NAME:	
JOB LOCATION:	
CONTRACTOR:	
CONTRACTOR APPROVAL:	
CONTRACTOR APPROVAL DATE:	
CONTRACTOR PO NO.:	
ENGINEER:	
ENGINEER APPROVAL:	
ENGINEER APPROVAL DATE:	

NOTES:


1. ALL DIMENSIONS SHOWN IN TABLE ARE IN INCHES, UNLESS OTHERWISE NOTED & ARE ± 1 INCH (25MM).
2. ALL ITEMS SHOWN IN PHANTOM LINE ARE TO BE PROVIDED BY OTHERS.
3. ALL DIMENSIONS ARE SUBJECT TO CHANGE WITHOUT ANY NOTICE.
4. INSTALL UNIONS FITTINGS ON INLET & OUTLET PLUMBING CONNECTIONS.
5. PROVIDE A 2 FEET MINIMUM CLEARANCE ABOVE MINERAL TANK FOR FILLING MEDIA.
6. FOR INSTALLATIONS USING METAL PLUMBING, CONNECT A METAL BONDING STRAP TO INLET & OUTLET METAL PLUMBING TO MAINTAIN ELECTRICAL CONTINUITY.
7. PROVIDED SYSTEM SHALL NOT BE SUBJECT TO ANY VACUUM. IF RISK OF VACUUM IS PRESENT, INSTALL VACUUM RELIEF VALVE WATTS ORDERING CODE # 0550031 ON OUTLET LINE.
8. THE FULL WEIGHT OF THE PIPING AND VALVES MUST BE SUPPORTED BY PIPE HANGERS OR OTHER MEANS.
9. INLET AND OUTLET HEADERS NEED TO BE SIZED ACCORDING TO FLOW RATE REQUIREMENTS BY OTHERS.
10. LIMIT INLET PRESSURE TO NOT EXCEED MAXIMUM PUBLISHED OPERATING PRESSURE.
11. FLEX CONNECTORS MUST BE INSTALLED HORIZONTALLY ON INLET AND OUTLET CONNECTIONS.
12. USE DIELECTRIC UNIONS ON PLUMBING CONNECTIONS WHEN DISSIMILAR METALS ARE PRESENT.

MODELS OF 1465-50TM, OF1665-75TM ONEFLOW ANTI-SCALE SYSTEM DIMENSIONS (INCHES) & SPECIFICATIONS													
MODEL NO.	ORDERING CODE (EDP NO.)	MINERAL TANK SIZE	INLET	OUTLET	OVERALL HEIGHT (SEE NOTE 5)	OVERALL DEPTH	OVERALL WIDTH	SYSTEM INLET/OUTLET PIPE SIZE CONN. (NPT)	PEAK SERVICE FLOW GPM	MIN/MAX OPERATING TEMP F°	MIN/MAX OPERATING PRESSURE (PSI)	ESTIMATED OPERATING WEIGHT (LBS)	ESTIMATED SHIPPING WEIGHT (LBS)
OF1465-50TM	7100661	14 X 65	67.3	67.3	68.8	14.2	14.2	2.0	50.00	40/100	15/100	442.00	97.50
OF1665-75TM	7100662	16 X 65	67.3	67.3	68.8	16.2	16.2	2.0	75.00	40/100	15/100	521.00	119.75


		815 CHESTNUT ST. NORTH ANDOVER, MA 01845	TITLE: GENERAL INSTALLATION MODELS OF 1465-50TM, OF1665-75TM ONEFLOW ANTI-SCALE SYSTEMS MATERIAL: N/A OTHER: ESTIMATED WEIGHT: SEE TABLE	PART NO.: SEE TABLE FILE TYPE: CAD
DWG NO.: 77/2021	DATE: 7/7/2021	SHEET NO.: 2 OF 3	SUPERSEDES: SEE TABLE	REV:




TOP VIEW



FRONT VIEW



SIDE VIEW



ISOMETRIC VIEW

CLIENT PROJECT SIGN-OFF	
JOB NAME:	
JOB LOCATION:	
CONTRACTOR:	
CONTRACTOR APPROVAL:	
CONTRACTOR APPROVAL DATE:	
CONTRACTOR PO NO.:	
ENGINEER:	
ENGINEER APPROVAL:	
ENGINEER APPROVAL DATE:	

WATTS		815 CHESTNUT ST. NORTH ANDOVER, MA 01845	DATE: 7/7/2021	SCALE: NTS	SUPERSEDES: SEE TABLE	REV: 3 OF 3	NO NET SCALE DRAWING	TITLE: GENERAL INSTALLATION MODELS OF 1405-50TM, OF 1665-75TM ONEFLOW ANTI-SCALE SYSTEMS	PART NO: SEE TABLE	EST. WEIGHT: SEE TABLE (SHT. 2)	FILE TYPE: CAD	REV: D 1
--------------	--	---	----------------	------------	-----------------------	-------------	----------------------	--	--------------------	---------------------------------	----------------	----------



ISOMETRIC VIEW
MULTI-TANK SYSTEM