Engineering Specification

| Job Name ————— | Contractor — |
|--------------------|---|
| ob Name | Contractor |
| Job Location ————— | Approval ———————————————————————————————————— |
| Engineer | Contractor's P.O. No. |
| Approval ————— | Representative ———————————————————————————————————— |

LEAD FREE*

Series Gate Valve TS-OSY

21/2" - 12"

Series Gate Valve TS-OSY resilient wedge gate valve, available in sizes 2½" to 12", is recommended for fire main shutoff and distribution service. The ductile iron body, bonnet, and stuffing plate are coated with fusion bonded epoxy, applied in accordance with AWWA C550. Gate Valve TS-OSY features Lead Free* construction to comply with Lead Free* installation requirements. Certified to ANSI/NSF61 and 372.

The gate valve is operated by handwheel, contains a wedge fully encapsulated with EPDM rubber permanently bonded to the wedge, and meets ASTM D249. A supervisory switch is mounted to the gate valve to provide alert when the water supply to the sprinkler system is tampered with or being shut off.

Features

- Meets or exceeds AWWA C509 and C515 standards
- Bubble tight at 250 psi
- High flow characteristics
- 100% smooth passage without turbulent flow
- Anti-friction thrust bearing
- Solid, bronze stem nut and high-strength bronze stem
- Two O-ring seals above stem thrust collar
- High-strength iron wedge fully encapsulated with rubber permanently bonded to metal
- High-strength ductile iron body, bonnet, and stuffing box
- Corrosion-resistant coating on interior and exterior surfaces of valve body
- Available in flange by flange, flange by groove or groove by groove

NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.

Inquire with governing authorities for local installation requirements.



Gate Valve TS-OSY with Supervisory Switch

Specification

Series TS-OSY shall be a resilient wedge gate valve manufactured to ASTM A536 ductile iron, rated for 250 psig working pressure, and hydrostatically proficient for shell leakage at pressures up to 500 psig. The gate valve shall comply with ANSI/AWWA C515 Standard for reduced-wall, resilient seated gate valves for water supply service. The valve shall have approvals from UL (UL262 - Gate Valves for Fire Protection Service) and FM (FM1120/1130 - Standard for Fire Service Water Control Valves). The bond of the rubber wedge closure member shall comply for adhesion per the ASTM D429 Standard. The end flanges of all flanged valves shall conform to the dimensions and drillings of the ANSI/ASME Standard B16.I, Class 125. Mechanical joint bell dimensions shall conform to ANSI/AWWA C111/A21.11. The end flange of tapping valves shall conform to MSS Standard Practice SP-60. All non-machined, interior, and exterior surfaces of the valve shall be coated with an inert, thermosetting epoxy resin to provide a corrosion-resistant coating that complies with the performance requirements of ANSI/ AWWA C550 Standard The valve shall have NSF International certification and comply with NSF61 and NSF372 standards. The valve shall be supplied with EPDM wedges. The temperature rating for valve shall be 33 to 125 degrees Fahrenheit, as required in the AWWA C509 standard.



^{*}The wetted surface of this product contacted by consumable water contains less than 0.25% of lead by weight.

Standards

Water supply service ANSI/AWWA C515

ANSI/ASME Standard B16.I, End flanges

Class 125

Mechanical joint bell dimensions ANSI/AWWA C111/A21.11

ANSI/AWWA C550 Interior coating Temperature AWWA C509

Approvals







Parts

Call customer service if you need assistance with technical details.

| SIZE | DESCRIPTION | MATERIAL |
|------|-------------------|---|
| 1 | Hold Down Nut | Bronze ASTM B584 C87850/C57610 |
| 2 | Yoke Nut | Bronze ASTM B584 C86700 |
| 3 | Handwheel | Ductile Iron ASTM A536 70-50-05 |
| 4 | Hex Cap Screw | ZN A307 Grade B/ASTM F593 S30400/S31600 |
| 5 | Yoke | Ductile Iron ASTM A536 70-50-05 |
| 6 | Hex Nut | ZN A307 Grade B/ASTM F593 S30400/S31600 |
| 7 | Packing Gland | Ductile Iron ASTM A536 70-50-05 |
| 8 | Hex Nut | ZN A307 Grade B/ASTM F593 S30400/S31600 |
| 9 | Hex Cap Screw | GR 2 ZN SAE J429/304SS ASTM 18-8SS |
| 10 | Hex Nut | ZN A307 Grade B/ASTM F593 S30400/S31600 |
| 11 | Yoke 0-ring | Buna-N ASTM D2000 |
| 12 | Stem | 304SS ASTM A276 S30400/316SS ASTM A276 |
| | | S31600/ECO Brass ASTM B371 C69300/Silicon |
| | | Bronnze "A" (Everdur) ASTM B98 C65500 |
| 13 | Hex Cap Screw | ZN A307 Grade B/ASTM F593 S30400/S31600 |
| 14 | Hex Nut | ZN A307 Grade B/ASTM F593 S30400/S31600 |
| 15 | Flat Washer | ZN A307 Grade B/ASTM F593 S30400/S31600 |
| 16 | Cover | Ductile Iron ASTM A536 70-50-05 |
| 17 | Cover 0-ring | Buna-N ASTM D2000 |
| 18 | Stem 0-ring | Buna-N ASTM D2000 |
| 19 | Stem Nut | Bronze ASTM B584 CDA 844 |
| 20 | Wedge | Ductile Iron ASTM A584 70-50-05 & EPDM |
| 21 | Body-flanged Type | Ductile Iron ASTM A584 70-50-05 |
| 22 | Packing | Braided, Lubricated (Non-asbestos) |

Coating


Pressure - Temperature

Material

250 neig

| Working pressure 250 | polg |
|-----------------------|------------|
| Temperature range 33° | F to 125°F |

Inert, thermosetting epoxy resin



Dimensions - Weights

| DIMENSION | | | | | | | | | | | | |
|-----------|-------|---------------------------------|-------|--------|-------|------|--------|--------|-----------|--------|----------------------|-------------|
| Size | А | В | С | D | E | F | G | Н | J | К | No. Turns to Open | Weight (lb) |
| 21/2 | 71/2" | 11/16" | 7" | 21/2" | 71/4" | 7" | 137/8" | 16%" | %" x 4 | 5½" | 8 | 52.00 |
| 3 | 8" | 3/4" | 71/2" | 3" | 10" | 7½" | 15%" | 187/8" | 5%" x 4 | 6" | 10 | 67.14 |
| 4 | 9" | ¹⁵ / ₁₆ " | 9" | 41/4" | 10" | 9" | 181/4" | 223/4" | 5%" x 4 | 7½" | 13½ | 91.85 |
| 6 | 10½" | 1" | 11" | 61/4" | 12" | 11%" | 23¾" | 301/%" | 3/4" x 8 | 91/2" | 19½ | 140.67 |
| 8 | 11½" | 11//8" | 13½" | 81/4" | 14" | 13½" | 291/4" | 37¾" | ¾" x 8 | 11¾" | 25½ | 212.60 |
| 10 | 13" | 13/16" | 16" | 101/4" | 18" | 16" | 35%" | 45¾" | ⅓" x 12 | 141/4" | 31½ | 368.48 |
| 12 | 14" | 11/4" | 19" | 121/4" | 18" | 19" | 40%" | 531/8" | 7⁄8" x 12 | 17" | 37¾" | 479.41 |



A WATTS Brand

USA: Backflow T: (978) 689-6066 • F: (978) 975-8350 • AmesFireWater.com

USA: Control Valves T: (713) 943-0688 • F: (713) 944-9445 • AmesFireWater.com

Canada: T: (888) 208-8927 • F: (905) 481-2316 • AmesFireWater.ca

Latin America: T: (52) 55-4122-0138 • AmesFireWater.com

ES-A-GateValve-TS-OSY 2425 © 2024 Watts